



Click [here](#) for the 3D model.

Dimensions

D	76.6mm +/-1mm
L	106mm +/-1mm
T	3.8mm NOM
S	32mm +/-0.5mm
F	15mm +/-0.5mm
DT	15mm NOM
G	13mm NOM
LT	113mm +/-1mm
Z	13mm NOM

Packaging Specifications

Sleeving	Yes
Packaging	Bulk, Bag

General Information

Series	PEH169_105
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	585 g
Notes	Dimensions D And L Include Sleeving. MS (MxH) = M12x16.

Specifications

Capacitance	3,300 uF
Capacitance Tolerance	-10/+30%
Voltage DC	250 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	13000 Hrs (Rated Voltage And Ripple Current At 105C)
ESR	36 mOhms (100Hz 20C), 20 mOhms (100kHz 20C)
Ripple Current	7.9 Amps (100Hz 105C), 41.5 Amps (10kHz 50C), 31.5 Amps (10kHz 40C)
Leakage Current	6475 uA (5min 20°C)
Inductance	17 nH (ESL)