

No Drawing Available.  
Click [here](#) for the 3D model.

## Dimensions

D	13.1mm +/-0.5mm
L	44.4mm +/-0.5mm
LL	142mm +/-5mm

## Packaging Specifications

Typical Component Weight	26
Packaging	Bulk
Packaging Quantity	1

## General Information

Style	Metal Sealed
Description	Metal Sealed Type Multilayer Piezoelectric Actuators
RoHS	With Exemptions
SCIP Number	c64eed42-9f3b-4f55-976e-a799ec5ecf68
Notes	Without Flange, V groove.
REACH	SVHC (PZT - CAS 12626-81-2)

## Specifications

Series	AHB
Displacement	52um +/-8um
Voltage DC	150 VDC
Capacitance	12 uF
Capacitance Tolerance	20%
Resonant Frequency	20 kHz
Generated Force	1700 N
Insulation Resistance	2 MOhms
Temperature Range	-25/+85°C