



Click [here](#) for the 3D model.

#### General Information

Series	ALP22
Dielectric	Aluminum Electrolytic
Description	Solder Pin, Aluminum Electrolytic
RoHS	Yes
Lead	5 Pin Solder
AEC-Q200	No
Typical Component Weight	95 g
Notes	Dimensions D And L Include Slewing.

#### Dimensions

D	40mm +/-1mm
L	55mm +/-2mm
S	20mm +/-0.1mm
LL	7.5mm +/-0.5mm
F	1.3mm

#### Packaging Specifications

Slewing	Yes
Packaging	Tray

#### Specifications

Capacitance	1,000 uF
Tolerance	20%
Voltage DC	200 VDC, 230 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	26000 Hrs
Leakage Current	1200 uA (5min 20°C)