



Click [here](#) for the 3D model.

General Information

Style	Metal Sealed
Description	Metal Sealed Type Multilayer Piezoelectric Actuators
RoHS	With Exemptions
SCIP Number	e8b63861-aef3-4ef5-83bb-6273ea2dbdde
Notes	Without Flange, V groove.
REACH	SVHC (PZT - CAS 12626-81-2)

Specifications

Series	ASL
Displacement	58um +/-9um
Voltage DC	150 VDC
Capacitance	3.9 uF
Tolerance	20%
Resonant Frequency	12 kHz
Generated Force	800 N
Insulation Resistance	10 MOhms
Temperature Range	-40/+150°C

Dimensions

D	13mm +/-0.5mm
L	64.4mm +/-0.5mm

Packaging Specifications

Typical Component Weight	22
Packaging	Tray
Packaging Quantity	10