



General Information	
Series	EFG
Style	Sheet
Description	Flex Suppressor Halogen Free Type
Features	High Frequency Specifications
RoHS	Yes
Qualifications	UL94 V-1
AEC-Q200	No
Environment	Halogen Free, PVC Free, Lead Free

Dimensions	
Sheet Size	240x240mm
L	240mm
W	240mm
T	0.2mm +/-0.05mm

Packaging Specifications	
Tape Description	No Adhesive Tape

Specifications	
Temperature Range	-40/+105°C
Permeability	20 u At 3MHz
Effective Frequency	10 GHz MAX
Specific Gravity	3 Atm TYP
Thermal Conductivity	0.22 W/m K

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.