



General Information

Series	EFH
Style	Sheet
Description	Flex Suppressor For High Temp, Reflow
Features	High Temperature Reflow
RoHS	Yes
Qualifications	UL94 V-0, UL File No. E176124
AEC-Q200	No
Environment	Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions

Sheet Size	240x240mm
L	240mm
W	240mm
T	0.1mm +/-0.03mm

Packaging Specifications

Tape Description	Without PET Tape (Txx00)
Adhesive Thickness	0.05 mm

Specifications

Temperature Range	-40/+105°C
Permeability	60 u At 3MHz
Effective Frequency	10 GHz MAX
Specific Gravity	3.1 Atm TYP
Thermal Conductivity	1.3 W/m K

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.