



## General Information

Series	EFR
Style	Sheet
Description	Flex Suppressor Halogen Free Type
Features	Standard Specifications
RoHS	Yes
Qualifications	UL94 V-0, UL File No. E176124
AEC-Q200	No
Environment	Halogen Free, PVC Free, Lead Free

## Dimensions

Sheet Size	240x240mm
L	240mm
W	240mm
T	1mm +/-0.2mm

## Packaging Specifications

Tape Description	No Adhesive Tape
------------------	------------------

## Specifications

Temperature Range	-40/+105°C
Permeability	60 u At 3MHz
Effective Frequency	10 GHz MAX
Specific Gravity	2.8 Atm TYP
Thermal Conductivity	0.22 W/m K