



Click [here](#) for the 3D model.

General Information

Series	ESD-R-B
Style	Round - Snail
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores
Features	Snail Shaped Case
RoHS	Yes
Qualifications	UL94 V-2
AEC-Q200	No
Case Color	Black
Toroidal	ESD-R-25SD
Materials	Ni-Zn
Core	Ni-Zn Ferrite

Specifications

Temperature Range	-25/+60°C
Effective Frequency	500 MHz (FM Band Range)

Dimensions

D	29.3mm +/-1.0mm
D2	13.9mm +/-1.0mm
L	23mm +/-1.0mm
T	15mm MAX

Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	300
Typical Component Weight	21.8 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.