


## SMC12.7155J50B31TR24

Aliases (F125YR155J050V, SMC100ZB7150JB31T1)

SMC/F125, Film, Metallized PPS, General Purpose, 1.5 uF, 5%, 50 VDC, 30 VAC, 100°C, 5045, 6.5mm



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

### Dimensions

Chip Size	5045
L	12.7mm +/-0.2mm
W	11.5mm +/-0.2mm
T	6.5mm +/-0.2mm
F	0.5mm NOM

### Packaging Specifications

Packaging	T&R
Packaging Quantity	600

### General Information

Series	SMC/F125
Dielectric	Metallized PPS
Style	SMD Chip
Features	High Stability
RoHS	Yes
AEC-Q200	No
Typical Component Weight	2.833 g
Shelf Life	104 Weeks
MSL	2

### Specifications

Capacitance	1.5 uF
Capacitance Tolerance	5%
Voltage DC	50 VDC
Voltage AC	30 VAC
Temperature Range	-55/+125°C
Rated Temperature	100°C
Dissipation Factor	0.15% 1kHz, 0.3% 10kHz
Insulation Resistance	3.3333 GOhms
Max dV/dt	3 V/us