



Click [here](#) for the 3D model.

### General Information

Series	GL-C
Style	Inlet
Description	Noise Filters
Features	Inlet Type
RoHS	Yes
Qualifications	UL, CSA
Miscellaneous	30 K Self-Temperature Rise Max.

### Dimensions

L	67mm NOM
W	52mm NOM
H	26mm NOM

### Packaging Specifications

Typical Component Weight	55 g
--------------------------	------

### Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Voltage	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	6 A (AC/DC)
Ripple Current	6 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	0.005 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.