



Click [here](#) for the 3D model.

Dimensions

Chip Size	0805
L	2mm +0.3/-0.1mm
W	1.25mm +/-0.2mm
T	0.85mm +/-0.2mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	4000

General Information

Series	L-SMS
Style	SMD Multi-Layer
Core	Ceramic
Description	Shielded, Surface Mount Inductor
Features	Standard Type
RoHS	Yes
Winding Type	Multilayer
Notes	Suggested Replacement - https://productfinder.pulseelectronics.com/part/BSCL002012091R0K00 .

Specifications

Inductance	1000 nH
Inductance Tolerance	10%
Temperature Range	-40/+85°C
Current	50 mAmps (MAX)
DC Resistance	0.4 Ohms
Quality Factor	45 at 10 MHz
Self-Resonant Frequency	75 MHz