



Click [here](#) for the 3D model.

#### General Information

Series	L-PWS
Style	SMD Wire-Wound
Core	Ferrite
Description	Surface Mount Inductor
Features	Standard Type
RoHS	Yes
Notes	Last Order Date June 30, 2023.

#### Dimensions

Chip Size	1207
L	3.2mm +/-0.2mm
W	1.8mm +/-0.2mm
T	1.8mm +/-0.2mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	2000

#### Specifications

Inductance	1000 uH (0.252 MHz)
Inductance Tolerance	20%
Rated Current	39 mAmps (MAX)
Temperature Range	-40/+105°C
DC Resistance	27 Ohms
DC Resistance	27 Ohms
Self-Resonant Frequency	2.4 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.