



Click [here](#) for the 3D model.

General Information

Series	L-DWD
Style	SMD Wire-Wound
Core	Ferrite
Description	Shielded, Surface Mount Inductor
Features	Low Profile
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - https://productfinder.pulseelectronics.com/part/BWVS00606045330M00 .

Dimensions

Chip Size	8040(3131)
L	8mm +/-0.2mm
W	8mm +/-0.2mm
T	4.2mm MAX
S	5.6mm +/-0.3mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	1000

Specifications

Inductance	33 uH (100 kHz)
Inductance Tolerance	20%
Rated Current	1700 mAmps (MAX)
Temperature Range	-25/+120°C
Shielded	Yes
DC Resistance	100 mOhms
DC Resistance	0.1 Ohms
Self-Resonant Frequency	12 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.