



Click [here](#) for the 3D model.

### Dimensions

L	24mm MAX
H	14mm MAX
T	7.6mm MAX
S	20.3mm +0.6/-0.1mm
H0	18.5mm +/-0.5mm
F	0.8mm +/-0.05mm

### Packaging Specifications

Packaging	T&R
Packaging Quantity	250

### General Information

Series	PMR209
Dielectric	Metallized Paper
Style	Radial
Features	RC Unit approved
RoHS	Yes
Lead	Wire Leads
Qualifications	ENEC, UL, cUL
AEC-Q200	No
Construction	Molded
Component Weight	3.6 g
Miscellaneous	Resistor= 100 Ohms.
Notes	Not For New Design, Please Use The New P409 Series @ 275 VAC.

### Specifications

Capacitance	0.1 uF
Capacitance Tolerance	20%
Voltage AC	250 VAC
Voltage DC	630 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	3 GOhms
Safety Class	X2