



Click [here](#) for the 3D model.

General Information

Series	SC-D
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Ni-Zn Ferrite

Dimensions

D	23mm MAX
T	13mm MAX
LL	15mm +/-2mm
S	6mm
S1	8mm
Wire Size	0.6mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	360
Typical Component Weight	8 g

Specifications

Voltage AC	250 VAC
Inductance	50 uH
Current	3 A
Temperature Range	-40/+105°C
DC Resistance	40 mOhms