



Click [here](#) for the 3D model.

Dimensions	
D	55mm MAX
H	30mm MAX
LL	15mm +/-2mm
S	42mm
S1	18mm
Wire Size	1.8mm x 2P

Packaging Specifications	
Packaging	Tray
Packaging Quantity	90
Typical Component Weight	103 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	0.5 mH (10 kHz)
Current	30 A
Temperature Range	-40/+105°C
DC Resistance	3 mOhms