



Click [here](#) for the 3D model.

Dimensions	
D	30mm MAX
H	21mm MAX
LL	10mm +/-2mm
S	15mm
S1	20mm
Wire Size	1mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	500
Typical Component Weight	25.7 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	2.6 mH (1 kHz)
Current	8 A
Temperature Range	-40/+120°C
DC Resistance	30 mOhms