



Click [here](#) for the 3D model.

### Dimensions

D	30.5mm MAX
T	23mm MAX
H	31.5mm MAX
LL	4mm +/-1.3mm
S	18mm NOM
S1	16mm NOM
Wire Size	0.9mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	33.7 g

### General Information

Series	SCR22
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 70 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	9 mH
Current	5 A
Temperature Range	-40/+120°C
DC Resistance	55 mOhms