



Click [here](#) for the 3D model.

Dimensions

D	32mm MAX
T	30mm MAX
H	24mm MAX
LL	5mm +/-2mm
S	10mm NOM
S1	25mm NOM
Wire Size	0.9mm

Packaging Specifications

Typical Component Weight	34 g
--------------------------	------

General Information

Series	SCR22
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	65 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	10 mH
Current	5 A
Temperature Range	-40/+120°C
DC Resistance	60 mOhms