



Click [here](#) for the 3D model.

General Information

Series	SCR25
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	80 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Dimensions

D	35mm MAX
T	26mm MAX
H	35mm MAX
LL	4mm +/-1mm
S	14mm NOM
S1	18mm NOM
Wire Size	1.1mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	180
Typical Component Weight	48 g

Specifications

Voltage AC	250 VAC
Inductance	7000 uH
Rated Current	7 A
Temperature Range	-40/+120°C
DC Resistance	34 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.