



Click [here](#) for the 3D model.

Dimensions	
L	9mm MAX
W	10mm MAX
H	10.5mm MAX
LL	3mm +/-0.7mm
S	6.5mm MAX

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	3000
Typical Component Weight	1.12 g

General Information	
Series	SH
Style	Through-Hole
RoHS	Yes
Miscellaneous	For 2 Lines.

Specifications	
Voltage DC	50 VDC
Inductance	30 uH
Temperature Range	-25/+60°C
DC Resistance	51 mOhms (per Line MAX)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.