

SNT-S20

Aliases (UDLSNT0S200000)

Differential Mode Chokes - Signal, KEMET, SNT, Through-Hole, Common Mode, 6,000 nH



Click [here](#) for the 3D model.

General Information

Series	SNT
Style	Through-Hole
RoHS	Yes

Dimensions

L	9.5mm MAX
W	5mm MAX
T	5mm MAX
H	12.7mm MAX
LL	5mm +/-1mm
S	5mm +/-0.2mm
F	0.5mm NOM

Specifications

Inductance	6 uH
Temperature Range	-20/+60°C
DC Resistance	35 mOhms (MAX)

Packaging Specifications

Packaging	Bulk
Packaging Quantity	100
Typical Component Weight	850 mg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.