



General Information

Series	SS17VA/HA
Style	Through-Hole Bobbin
RoHS	Yes
Notes	recommended replacement part SSR10VS-10135.
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530 or equivalent.

Dimensions

L	17mm +/-1mm
T	12mm +/-1mm
H	15.1mm +/-1mm
LL	3.5mm +/-1mm
S	12mm +/-1mm
S1	8mm +/-1mm
Wire Size	0.37mm
F	0.6mm +/-0.1mm

Packaging Specifications

Typical Component Weight	6 g
--------------------------	-----

Specifications

Voltage AC	250 VAC
Inductance	2.5 mH
Rated Current	1 A
Temperature Range	-25/+120°C
DC Resistance	0.38 Ohms