



Click [here](#) for the 3D model.

#### General Information

Series	SS21V
Style	Through-Hole Bobbin
RoHS	Yes
Notes	Replacement For SS24V Type And SSI 1 V Type.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

#### Dimensions

L	20.6mm +/-1mm
T	16.8mm +/-1mm
H	24.5mm +/-1mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.25mm
F	0.8mm +/-0.1mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	12.2 g

#### Specifications

Voltage AC	250 VAC
Inductance	54 mH
Rated Current	500 mA
Temperature Range	-40/+120°C
DC Resistance	2.4 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.