



#### General Information

Series	SS28V/H-CH
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

#### Dimensions

L	30mm MAX
T	30mm MAX
H	24.5mm MAX
LL	4mm +/-1mm
S	24mm +/-0.5mm
S1	20mm +/-0.5mm
F	0.8mm NOM

#### Specifications

Voltage AC	250 VAC
Inductance	7.5 mH
Rated Current	2 A
Temperature Range	-25/+120°C
DC Resistance	0.22 Ohms

#### Packaging Specifications

Typical Component Weight	30.3 g
--------------------------	--------