



Click [here](#) for the 3D model.

#### General Information

Series	SSR10VS/HS
Style	Through-Hole Bobbin
Features	Compact Size, Low Profile, Light Weight, High Frequency, Broad Bandwidth
RoHS	Yes
Miscellaneous	50 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

#### Dimensions

L	22mm MAX
T	18mm MAX
H	13.5mm MAX
LL	3.5mm +/-0.5mm
S	17mm +/-0.5mm
S1	12mm +/-0.5mm
Wire Size	0.23mm
F	0.7mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	9 g

#### Specifications

Voltage AC	250 VAC
Inductance	49.5 mH
Rated Current	500 mA
Temperature Range	-25/+120°C
DC Resistance	1.6 Ohms