



General Information

Series	SSR21H
Style	Through-Hole Bobbin
RoHS	Yes

Dimensions

L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.35mm
F	0.8mm NOM

Specifications

Voltage AC	250 VAC
Inductance	21500 uH
Rated Current	1 A
Temperature Range	-25/+120°C
DC Resistance	0.41 Ohms

Packaging Specifications

Typical Component Weight	14 g
--------------------------	------