



#### General Information

|        |                     |
|--------|---------------------|
| Series | SSR21H              |
| Style  | Through-Hole Bobbin |
| RoHS   | Yes                 |

#### Dimensions

|           |                 |
|-----------|-----------------|
| L         | 23mm MAX        |
| T         | 23mm MAX        |
| H         | 14.5mm MAX      |
| LL        | 3.5mm +/-0.5mm  |
| S         | 10mm +/-0.5mm   |
| S1        | 18.5mm +/-0.5mm |
| Wire Size | 0.4mm           |
| F         | 0.8mm NOM       |

#### Specifications

|                   |            |
|-------------------|------------|
| Voltage AC        | 250 VAC    |
| Inductance        | 12000 uH   |
| Rated Current     | 1.3 A      |
| Temperature Range | -25/+120°C |
| DC Resistance     | 0.24 Ohms  |

#### Packaging Specifications

|                          |      |
|--------------------------|------|
| Typical Component Weight | 14 g |
|--------------------------|------|