



#### General Information

Series	SSR21HS
Style	Through-Hole Bobbin
RoHS	Yes

#### Dimensions

L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.3mm
F	0.8mm NOM

#### Specifications

Voltage AC	250 VAC
Inductance	24500 uH
Rated Current	700 mA
Temperature Range	-25/+120°C
DC Resistance	0.59 Ohms

#### Packaging Specifications

Typical Component Weight	14 g
--------------------------	------