



General Information

| | |
|--------|---------------------|
| Series | SSR21HS |
| Style | Through-Hole Bobbin |
| RoHS | Yes |

Dimensions

| | |
|-----------|-----------------|
| L | 23mm MAX |
| T | 23mm MAX |
| H | 14.5mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 10mm +/-0.5mm |
| S1 | 18.5mm +/-0.5mm |
| Wire Size | 0.5mm |
| F | 0.8mm NOM |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 2900 uH |
| Rated Current | 2 A |
| Temperature Range | -25/+120°C |
| DC Resistance | 0.1 Ohms |

Packaging Specifications

| | |
|--------------------------|------|
| Typical Component Weight | 14 g |
|--------------------------|------|