



Click [here](#) for the 3D model.

#### General Information

Series	SU-9VF
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	1500 uH
Rated Current	700 mA
Temperature Range	-25/+120°C
DC Resistance	0.44 Ohms

#### Dimensions

L	17mm MAX
T	11mm MAX
H	17mm MAX
LL	3mm MIN
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.23mm
F	0.6mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	1000
Typical Component Weight	3.3 g