



General Information	
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, Molded, High Temperature
Features	High Temperature
RoHS	Yes
Termination	Gold
AEC-Q200	No
Notes	Old Part Number [Obsolete] Was B45198P1106K106.

Specifications	
Capacitance	10 uF
Capacitance Tolerance	10%
Voltage DC	6.3 VDC (85C), 5.02 VDC (125C), 4.22 VDC (150C)
Temperature Range	-55/+150°C
Rated Temperature	85°C
Dissipation Factor	4.5%
Failure Rate	N/A
ESR	2.7 Ohms (100kHz)
Leakage Current	0.6 uA

Dimensions	
Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
S	0.8mm +/-0.3mm
F	1.2mm +/-0.1mm
K	1.3mm TYP

Packaging Specifications	
Packaging	T&R, 330mm
Packaging Quantity	9000