



Click [here](#) for the 3D model.

General Information	
Series	UB2
Style	SMD
Description	Miniature Signal Relay, Single Coil Latch
Features	Super-Compact Size, Flat-Package
RoHS	Yes
Coil Type	Single Coil (Latching)

Dimensions	
H	9mm MAX
L	10.6mm +/-0.3mm
W	5.7mm +/-0.3mm
LL	1.2mm NOM
S	3.2mm +/-0.15mm
S1	2.2mm +/-0.15mm
F	0.8mm +/-0.1mm
F1	2.25mm +/-0.1mm

Packaging Specifications	
Packaging	Tube

Specifications	
Temperature Range	-40/+85°C
Coil Voltage	3 V
Contact Form	2 Form C (DPDT)
Switching Current	1 A
Coil Resistance	90 Ohms +/-10%
Contact Material	Silver alloy with gold alloy overlay
Voltage Characteristics	2.25 (Set/Reset)
Power	100 mW
Switching Power	30 W, 37.5 VA
Switching Voltage DC	220 V
Switching Voltage AC	250 VAC
Contact Current Class	>10A
Carrying Current	1 Amps
Contact Resistance	100 mOhms
Operation Time	Approximately 2ms
Release Time	Approximately 1ms
Insulation Resistance	1 GOhms
Withstanding Voltage	1000 VAC (1min) 1500 V Surge

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.