

**Sample Kit Contents**

Part Number	Series	Thickness	Tape Thickness	Relative Magnetic Permeability	Specific Gravity	Tensile Strength	Surface Resistance	Thermal Conductivity
		mm	mm	@ 3 MHz	Typical	Mpa Minimum	$\Omega$ Minimum	W/m K
EFA(01)-240x240T0800	EFA	0.1	0.03	60	3.1	6.8	$1.0 \times 10^6$	1.3
EFA(03)-240x240T0800	EFA	0.3	0.03	60	3.1	6.8	$1.0 \times 10^6$	1.3
EFF(01)-240x240T0800	EFF	0.1	0.03	130	3.6	6.9	$1.0 \times 10^5$	0.4
EFF(03)-240x240T0800	EFF	0.3	0.03	130	3.6	6.9	$1.0 \times 10^5$	0.4
EFG(01)-240x240T0800	EFG	0.1	0.03	20	3	3.5	$1.0 \times 10^5$	0.22
EFG(03)-240x240T0800	EFG	0.3	0.03	20	3	3.5	$1.0 \times 10^5$	0.22
EFX(03)-240x240T0800	EFX	0.3	0.03	100	3.2	6.8	$1.0 \times 10^5$	0.22
EFX(05)-240x240T1500	EFX	0.5	0.14	100	3.2	6.8	$1.0 \times 10^5$	0.22
EFR(10)-240x240T1500	EFR	1	0.14	60	2.8	3.6	$1.0 \times 10^6$	0.22

*Kit contains one (1) 120 x 120 mm sheet of each part number listed above.*