



Specifications	
Voltage AC	250 VAC
Voltage DC	350 VDC
Rated Frequency	50-60 Hz
Rated Current	200 A
Ripple Current	200 A
Rated Temperature	40°C
Temperature Range	-40/+85°C
Climate Category	40/085/56

Dimensions	
A	49.5mm MIN
B	185mm MIN
D1	Threaded Studs M10
Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1

© 2006 - 2025 YAGEO