SCR31B-105-1R4A055JH

Aliases (UALF11R4A055JH)

Common Mode Chokes - Power, KEMET, SCR31, Through-Hole, Common Mode, 5,500 uH



Click here for the 3D model.

General Information	
Series	SCR31
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	80 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Dimensions	
D	48mm MAX
T	42mm MAX
H	35mm MAX
LL	4mm +/-1mm
S	17mm NOM
S1	30mm NOM
Wire Size	1.4mm

Specifications	
Voltage AC	500 VAC
Inductance	5500 uH
Rated Current	10.5 A
Temperature Range	-40/+120°C
DC Resistance	22 mOhms

Packaging Specifications	
Packaging	Tray
Packaging Quantity	80
Typical Component Weight	84 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2025 YAGEO