

Overview

The C4C capacitor is a polypropylene metallized film and polyester double-metallized foil capacitor with a polyester tape wrapping filled with resin, and uses tinned copper wires.

Applications

Typical applications include snubber, clamping, resonance, coupling/decoupling, pulse, and blocking.

Benefits


- Self-healing
- Low loss
- High ripple current
- High contact reliability
- Suitable for high frequency applications
- PP metallized and PET double-sided metallized foil



Part Number System

| C4 | C | A | M | U | B | 3100 | AA | 0 | J |
|---------------------|-------------------------------------|--|--|--|-------------------------------|--|---|----------------------------|-------------------|
| Series | Type | Fire Protection | Rated Voltage (VDC) | Insulation | Lead Diameter (mm) | Capacitance Code (pF) | Packaging | Capacitor Length (mm) | Tolerance |
| C4 = MKP Capacitors | C = Round body, snubber application | A = No fire retardant S = Fire retardant (on request) | M = 850 P = 1,200 W = 2,000 Y = 3,000 | U = Polyester tape and resin protection 0 = Uninsulated (upon request, but not in combination with Fire Protection "S") | B = 0.8 C = 1.0 D = 1.2 | Digits two – four indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added. | AA = Bulk (Bag) – straight leads see "Dimensions Table" | 0 = 33 1 = 44 3 = 58 | J = 5% K = 10% |

Dimensions – Millimeters



| D | L | d | LL |
|-------------|---------|---------|----|
| Maximum | Maximum | Nominal | ±5 |
| 10 – 14 | 33 | 0.8 | 40 |
| 14.5 – 21.5 | 33 | 1 | 40 |
| 19 – 23 | 44 | 1 | 40 |
| 23.5 – 33.5 | 44 | 1.2 | 40 |
| 28.5 – 32 | 58 | 1.2 | 40 |

Qualification

| | |
|-------------------------------|-------------------------------|
| Reference Standards | VDE 0560, IEC 61071, EN 61071 |
| Application Class (DIN 40040) | GPE/LS |
| Vibration Strength | DIN 40040, Table 6, Class V |

Performance Characteristics

| | |
|--|--|
| Temperature Range | -40°C to +85°C |
| Maximum Permissible Ambient Temperature | +70°C |
| IEC Climatic Category | 40/85/56 according to IEC 68-1 |
| Peak Non-Repetitive Maximum Current | $I_{PKR} \times 1.5$ |
| Test Voltage Terminal to Terminal (VTT) | $2 V_n$ for 10 seconds |
| Test Voltage Terminal to Case (VTC) | 3 k VDC 50 Hz for 60 seconds |
| Insulation Resistance Test Conditions | Temperature: +25°C ±5% Voltage charge time: 1 minute Test voltage: 100 VDC Typical value (Ris x C): 3,000 seconds |
| Dissipation Factor (DF) | $\leq 5 \times 10^{-4}$ at 1 kHz and 20°C |
| Capacitance Deviation in Operating Temperature Range of -40°C to +85°C | ±1.5% maximum on capacitance value measured at +20°C |
| Life Expectancy | $\geq 30,000$ hours at V_{RMS} $\geq 100,000$ hours at V_n |
| Failure Quota | 300/10 ⁹ components per hour |
| Change of Capacitance vs. Operating Time | -3% after 30,000 hours at V_{RMS} or after 100,000 hours at V_n |
| Protection | Polyester wrapping with epoxy resin fill |
| Flame Retardant (IEC 384-1) | Standard execution: non-flame retardant On request: flame retardant execution Category C |
| Leads | Tinned copper |
| Installation | Any position |
| Damp Heat Test | Test Conditions |
| | Relative humidity: 93% ±2% |
| | Temperature: +40°C |
| | Test duration: 56 days |
| | Capacitance change: $\leq \pm 5\%$ |
| | DF change: $\leq 50\%$ of nominal value at 1 kHz |
| | Insulation resistance: $\geq 50\%$ of limit value |

Table 1 – Ratings & Part Number Reference

| Cap Value (µF) | VDC | VAC | Peak VDC | Maximum Dimensions (mm) | | Ripple Current | Peak Current | ESR (Max) | dV/dt (V/µs) | Packaging Quantity | Part Number |
|------------------------|-------|-----|----------|-------------------------|--------|------------------|--------------|--------------|--------------|--------------------|-----------------------|
| | | | | D | L | 100 kHz 70°C (A) | (A) | 100 kHz (mΩ) | | | |
| 0.1 | 850 | 450 | 1,200 | 10.5 | 33 | 5 | 45 | 16.6 | 450 | 300 | C4C(1)M(2)B3100AA0(3) |
| 0.15 | 850 | 450 | 1,200 | 12.5 | 33 | 7 | 68 | 11.5 | 450 | 300 | C4C(1)M(2)B3150AA0(3) |
| 0.22 | 850 | 450 | 1,200 | 15.5 | 33 | 9 | 99 | 8.1 | 450 | 200 | C4C(1)M(2)C3220AA0(3) |
| 0.33 | 850 | 450 | 1,200 | 18.5 | 33 | 9 | 149 | 5.8 | 450 | 150 | C4C(1)M(2)C3330AA0(3) |
| 0.47 | 850 | 450 | 1,200 | 21.5 | 33 | 9 | 212 | 4.6 | 450 | 100 | C4C(1)M(2)C3470AA0(3) |
| 0.68 | 850 | 450 | 1,200 | 21 | 44 | 9 | 204 | 5.1 | 300 | 100 | C4C(1)M(2)C3680AA1(3) |
| 1 | 850 | 450 | 1,200 | 25 | 44 | 12 | 300 | 3.8 | 300 | 50 | C4C(1)M(2)D4100AA1(3) |
| 1.5 | 850 | 450 | 1,200 | 30.5 | 44 | 12 | 450 | 3.1 | 300 | 50 | C4C(1)M(2)D4150AA1(3) |
| 2 | 850 | 450 | 1,200 | 28.5 | 58 | 12 | 400 | 3.8 | 200 | 30 | C4C(1)M(2)D4200AA3(3) |
| 2.2 | 850 | 450 | 1,200 | 29.5 | 58 | 12 | 440 | 3.7 | 200 | 30 | C4C(1)M(2)D4220AA3(3) |
| 2.5 | 850 | 450 | 1,200 | 31.5 | 58 | 12 | 500 | 3.5 | 200 | 30 | C4C(1)M(2)D4250AA3(3) |
| 0.047 | 1,200 | 500 | 1,600 | 10 | 33 | 4 | 33 | 27.1 | 700 | 400 | C4C(1)P(2)B2470AA0(3) |
| 0.068 | 1,200 | 500 | 1,600 | 12 | 33 | 5 | 48 | 19.1 | 700 | 300 | C4C(1)P(2)B2680AA0(3) |
| 0.1 | 1,200 | 500 | 1,600 | 14 | 33 | 7 | 70 | 13.4 | 700 | 250 | C4C(1)P(2)B3100AA0(3) |
| 0.15 | 1,200 | 500 | 1,600 | 17.5 | 33 | 9 | 105 | 9.2 | 700 | 150 | C4C(1)P(2)C3150AA0(3) |
| 0.22 | 1,200 | 500 | 1,600 | 20.5 | 33 | 9 | 154 | 6.8 | 700 | 100 | C4C(1)P(2)C3220AA0(3) |
| 0.33 | 1,200 | 500 | 1,600 | 20 | 44 | 9 | 149 | 7.2 | 450 | 100 | C4C(1)P(2)C3330AA1(3) |
| 0.47 | 1,200 | 500 | 1,600 | 23 | 44 | 9 | 212 | 5.6 | 450 | 70 | C4C(1)P(2)C3470AA1(3) |
| 0.68 | 1,200 | 500 | 1,600 | 27.5 | 44 | 12 | 306 | 4.2 | 450 | 50 | C4C(1)P(2)D3680AA1(3) |
| 1 | 1,200 | 500 | 1,600 | 33 | 44 | 12 | 450 | 3.5 | 450 | 50 | C4C(1)P(2)D4100AA1(3) |
| 1.2 | 1,200 | 500 | 1,600 | 29 | 58 | 12 | 330 | 4.5 | 275 | 30 | C4C(1)P(2)D4120AA3(3) |
| 1.5 | 1,200 | 500 | 1,600 | 32 | 58 | 12 | 413 | 4 | 275 | 30 | C4C(1)P(2)D4150AA3(3) |
| 0.022 | 2,000 | 630 | 2,400 | 10.5 | 33 | 3 | 25 | 48.2 | 1,150 | 400 | C4C(1)W(2)B2220AA0(3) |
| 0.033 | 2,000 | 630 | 2,400 | 12.5 | 33 | 4 | 38 | 32.5 | 1,150 | 300 | C4C(1)W(2)B2330AA0(3) |
| 0.047 | 2,000 | 630 | 2,400 | 15 | 33 | 6 | 54 | 23 | 1,150 | 200 | C4C(1)W(2)C2470AA0(3) |
| 0.068 | 2,000 | 630 | 2,400 | 17.5 | 33 | 7 | 78 | 16.3 | 1,150 | 150 | C4C(1)W(2)C2680AA0(3) |
| 0.1 | 2,000 | 630 | 2,400 | 20.5 | 33 | 9 | 115 | 11.6 | 1,150 | 100 | C4C(1)W(2)C3100AA0(3) |
| 0.15 | 2,000 | 630 | 2,400 | 19.5 | 44 | 9 | 105 | 11.3 | 700 | 100 | C4C(1)W(2)C3150AA1(3) |
| 0.22 | 2,000 | 630 | 2,400 | 23.5 | 44 | 12 | 154 | 8 | 700 | 70 | C4C(1)W(2)D3220AA1(3) |
| 0.33 | 2,000 | 630 | 2,400 | 28.5 | 44 | 12 | 231 | 5.9 | 700 | 50 | C4C(1)W(2)D3330AA1(3) |
| 0.47 | 2,000 | 630 | 2,400 | 33.5 | 44 | 12 | 329 | 4.8 | 700 | 50 | C4C(1)W(2)D3470AA1(3) |
| 0.56 | 2,000 | 630 | 2,400 | 29 | 58 | 12 | 224 | 6.1 | 400 | 30 | C4C(1)W(2)D3560AA3(3) |
| 0.68 | 2,000 | 630 | 2,400 | 32 | 58 | 12 | 272 | 5.4 | 400 | 30 | C4C(1)W(2)D3680AA3(3) |
| 0.0068 | 3,000 | 750 | 3,500 | 10 | 33 | 2 | 14.5 | 132 | 2,100 | 400 | C4C(1)Y(2)B1680AA0(3) |
| 0.01 | 3,000 | 750 | 3,500 | 12 | 33 | 3 | 21 | 90.3 | 2,100 | 300 | C4C(1)Y(2)B2100AA0(3) |
| 0.015 | 3,000 | 750 | 3,500 | 14.5 | 33 | 4 | 32 | 60.5 | 2,100 | 200 | C4C(1)Y(2)C2150AA0(3) |
| 0.022 | 3,000 | 750 | 3,500 | 17 | 33 | 5 | 46 | 41.6 | 2,100 | 150 | C4C(1)Y(2)C2220AA0(3) |
| 0.033 | 3,000 | 750 | 3,500 | 20.5 | 33 | 6 | 69 | 28.3 | 2,100 | 100 | C4C(1)Y(2)C2330AA0(3) |
| 0.047 | 3,000 | 750 | 3,500 | 19 | 44 | 7 | 59 | 25.7 | 1,250 | 100 | C4C(1)Y(2)C2470AA1(3) |
| 0.068 | 3,000 | 750 | 3,500 | 22.5 | 44 | 9 | 85 | 18.3 | 1,250 | 70 | C4C(1)Y(2)C2680AA1(3) |
| 0.1 | 3,000 | 750 | 3,500 | 27 | 44 | 12 | 125 | 12.8 | 1,250 | 50 | C4C(1)Y(2)D3100AA1(3) |
| 0.15 | 3,000 | 750 | 3,500 | 32 | 44 | 12 | 188 | 9.2 | 1,250 | 50 | C4C(1)Y(2)D3150AA1(3) |
| 0.22 | 3,000 | 750 | 3,500 | 31 | 58 | 12 | 165 | 9.5 | 750 | 30 | C4C(1)Y(2)D3220AA3(3) |
| Capacitance Value (µF) | VDC | VAC | Peak VDC | D (mm) | L (mm) | Ripple Current | Peak Current | ESR | dV/dt (V/µs) | Packaging Quantity | Part Number |

(1) A = No fire retardant; S = fire retardant (on request)

(2) U = Tape and resin protection; 0 = unprotected (upon request, but not in combination with Fire retardant code "S")

(3) K = ±10%, J = ±5%

Environmental Compliance

As a leading global supplier of electronic components and an environmentally conscious company, KEMET continually aspires to improve the environmental effects of our manufacturing processes and our finished electronic components.

In Europe (RoHS Directive) and in some other geographical areas such as China (China RoHS), legislation has been enacted to prevent or otherwise limit the use of certain hazardous materials, including lead (Pb), in electronic equipment. KEMET monitors legislation globally to ensure compliance and endeavors to adjust our manufacturing processes and/or electronic components as may be required by applicable law.

For military, medical, automotive, and some commercial applications, the use of lead (Pb) in the termination is necessary and/or required by design. KEMET is committed to communicating RoHS compliance to our customers. Information related to RoHS compliance will be provided in data sheets and using specific identifiers on the packaging labels.

All KEMET power film capacitors are RoHS compliant.

Materials & Environment

The selection of raw materials that KEMET uses for the production of its electronic components is the result of extensive experience. KEMET directs specific attention toward environmental protection. KEMET selects its suppliers according to ISO 9001 standards and performs statistical analyses on raw materials before acceptance for use in manufacturing our electronic components. All materials are, to the best of KEMET's knowledge, non-toxic and free from cadmium; mercury; chrome and compounds; polychlorine triphenyl (PCB); bromide and chlorinedioxins bromurate clorurate; CFC and HCFC; and asbestos.

Dissipation Factor

Dissipation factor is a complex function involved with capacitor inefficiency. The $\text{tg}\delta$ may vary up and down with increased temperature. For more information, refer to Performance Characteristics.

Sealing

Hermetically Sealed Capacitors


As the temperature increases, the pressure inside the capacitor increases. If the internal pressure is high enough, it can cause a breach in the capacitor. Such a breach can result in leakage, impregnation, filling fluid, or moisture susceptibility.

Barometric Pressure


The altitude at which hermetically sealed capacitors are operated controls the capacitor's voltage rating. As the barometric pressure decreases, the susceptibility to terminal arc-over increases. Non-hermetic capacitors can be affected by internal stresses due to pressure changes. These effects can be in the form of capacitance changes, dielectric arc-over, and/or low insulation resistance. Altitude can also affect heat transfer. Heat that is generated in an operation cannot be dissipated properly, and high RI^2 losses and eventual failure can result.

Soldering Process


The implementation of the RoHS Directive has required the selection SnAgCu (SAC) alloys or SnCu alloys as primary solder. This has increased the liquidus temperature from that of 183°C for SnPb eutectic alloy to 217 – 221°C for the new alloys. As a result, the heat stress to components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (melting point of polypropylene is 160 – 170°C). Wave soldering can be destructive especially for mechanically small polypropylene capacitors (lead spacings 5 – 10 mm) and great care must be taken during soldering. The solder profiles from KEMET are highly recommended. You may also refer to the wave soldering curve from IEC Publication 61760–1 Edition 2. Please consult KEMET with any questions.




Construction



Winding Scheme



Marking



Slight change in the layout can be possible but this does not affect the content of the information of the current marking. This change will be achieved without impact to product form, fit or function, as the products are equivalent with respect to physical, mechanical, quality and reliability characteristics.

KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

Additional information about production site flexibility can be found [here](#)

KEMET is a registered trademark of KEMET Electronics Corporation.