



Click [here](#) for the 3D model.

#### General Information

Series	HV RAD-LDD Indust COG HV
Style	Radial
Description	Commercial, High Voltage
Features	Commercial
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a>
Termination	Copper
Lead	Wire Leads
AEC-Q200	No

#### Dimensions

L	21.59mm MAX
H	10.16mm MAX
T	6.89mm MAX
S	17.78mm +/-0.762mm
LL	3.175mm MIN
F	0.635mm +0.102/-0.051mm

#### Packaging Specifications

Packaging	Waffle
Packaging Quantity	20

#### Specifications

Capacitance	0.02 uF
Tolerance	5%
Voltage DC	1000 VDC
Dielectric Withstanding Voltage	1,200 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	COG
Dissipation Factor	0.15%
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	50 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.