


ALC10A102BB100

Aliases (A521CD102M100A)

ALC10, Aluminum Electrolytic, 1,000 uF, 20%, 100 VDC, -40/+85°C



Click [here](#) for the 3D model.

Dimensions

| | |
|----|---------------|
| D | 25mm +1mm |
| L | 30mm +/-2mm |
| S | 10mm +/-0.1mm |
| LL | 6.3mm +/-1mm |
| F | 2mm +/-0.1mm |

Packaging Specifications

| | |
|-----------|-----------|
| Sleeving | Yes |
| Packaging | Bulk, Bag |

General Information

| | |
|--------------------------|--------------------------------------|
| Series | ALC10 |
| Dielectric | Aluminum Electrolytic |
| Description | Snap-In, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | 2 Pin |
| AEC-Q200 | No |
| Typical Component Weight | 28 g |
| Notes | Dimensions D And L Include Sleeving. |
| Shelf Life | 156 Weeks |

Specifications

| | |
|-----------------------|---|
| Capacitance | 1,000 uF |
| Capacitance Tolerance | 20% |
| Voltage DC | 100 VDC, 115 VDC (Surge) |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Life | 10000 Hrs (Rated Voltage And Ripple Current At 85C), 16000 Hrs (Rated Voltage At 85C) |
| ESR | 243 mOhms (100Hz 20C), 182 mOhms (10kHz 20C) |
| Ripple Current | 1.67 Amps (100Hz 85C), 2.04 Amps (10kHz 85C) |
| Leakage Current | 600 uA (5min 20°C) |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.