



Click [here](#) for the 3D model.

#### General Information

Series	A700
Dielectric	Polymer Aluminum
Style	SMD Chip
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Termination	Tin
Qualifications	UL94V-0
AEC-Q200	No
Halogen Free	Yes
Shelf Life	104 Weeks
MSL	3

#### Specifications

Capacitance	220 uF
Tolerance	20%
Voltage DC	2 VDC
Temperature Range	-55/+105°C
Rated Temperature	105°C
Life	2000 Hrs (105C)
Dissipation Factor	6% 120Hz 25C
ESR	9 mOhms (100kHz 25C)
Ripple Current	5900 mA (rms 100kHz)
Leakage Current	44 uA (5min 25°C)

#### Dimensions

L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	1.1mm +/-0.1mm
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm

#### Packaging Specifications

Packaging	T&R, 180mm
Packaging Quantity	1000