


FRONT VIEW



SIDE VIEW



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|---|
| Series | A70 |
| Dielectric | Metallized Polypropylene |
| Style | Axial |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |
| Typical Component Weight | 5.4 g |
| Miscellaneous | Above 85C DC And AC Voltage Derating Is 1.25%/C. maxKO = 320. |

Dimensions

| | |
|----|---------------|
| D | 17mm MAX |
| L | 33mm MAX |
| LL | 38mm MIN |
| F | 1mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 200 |

Specifications

| | |
|-----------------------|-------------------------|
| Capacitance | 4.7 uF |
| Tolerance | 10% |
| Voltage DC | 160 VDC, 120 VDC (105C) |
| Voltage AC | 90 VAC |
| Temperature Range | -55/+105°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.06% 1kHz |
| Insulation Resistance | 6.383 GOhms |
| Max dV/dt | 1 V/us |
| Inductance | 33 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.