



Click [here](#) for the 3D model.

Dimensions

D	18mm MAX
L	33mm MAX
F	1mm +/-0.05mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	200

General Information

Series	A72
Dielectric	Film/Foil Polypropylene
Style	Axial
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	10 g
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C. maxKO = 13000000.

Specifications

Capacitance	0.068 uF
Tolerance	10%
Voltage DC	1500 VDC, 1125 VDC (105C)
Voltage AC	450 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 10kHz, 0.1% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	4,500 V/us
Inductance	33 nH