



Click [here](#) for the 3D model.

### Dimensions

|             |                 |
|-------------|-----------------|
| D           | 8mm +/-0.5mm    |
| L           | 11.5mm +/-1.5mm |
| S           | 3.5mm +/-0.5mm  |
| LL Negative | 15mm MIN        |
| LL Positive | 19mm MIN        |
| F           | 0.6mm +/-0.05mm |

### Packaging Specifications

|           |           |
|-----------|-----------|
| Packaging | Bulk, Bag |
|-----------|-----------|

### General Information

|              |                                |
|--------------|--------------------------------|
| Series       | A750                           |
| Dielectric   | Polymer Aluminum               |
| Description  | Single Ended, Polymer Aluminum |
| RoHS         | Yes                            |
| Lead         | Wire Leads                     |
| AEC-Q200     | No                             |
| Halogen Free | Yes                            |

### Specifications

|                       |  |
|-----------------------|--|
| Capacitance           | 1,500 uF   |
| Capacitance Tolerance | 20%  |
| Voltage DC            | 2.5 VDC, 2.9 VDC (Surge)   |
| Temperature Range     | -55/+105°C   |
| Rated Temperature     | 105°C  |
| Life                  | 2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit) |
| Dissipation Factor    | 12% 120Hz 20C  |
| ESR                   | 7 mOhms (100kHz 20C)   |
| Ripple Current        | 6100 mAmps (100kHz 105C)   |
| Leakage Current       | 750 uA (2min 20°C)   |