



Click [here](#) for the 3D model.

General Information

Series	ACR Indust COG HT200C
Style	Radial
Description	Commercial, High Temperature
Features	Commercial
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	f2ec9c71-d741-45f9-8d01-f6de6baf235a
Termination	Gold
Lead	Wire Leads
Testing and Reliability	Standard
AEC-Q200	No

Dimensions

L	12.7mm MAX
W	12.7mm MAX
T	3.81mm MAX
S	10.16mm +/-0.38mm
LL	3.175mm MIN
F	0.635mm +/-0.051mm

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

Specifications

Capacitance	0.1 uF
Tolerance	5%
Voltage DC	25 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	COG
Dissipation Factor	0.15% 1 kHz 1.0Vrms
Insulation Resistance	10 GOhms