



Click [here](#) for the 3D model.

### Dimensions

D	10mm +/-0.5mm
L	10.2mm +/-0.5mm
W	10.3mm +/-0.2mm
H	10.3mm +/-0.2mm
C	11mm +/-0.2mm
P	4.6mm NOM
R	0.8 - 1.1mm

### Packaging Specifications

Packaging	T&R, 380mm
-----------	------------

### General Information

Series	A781
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Lead	V-Chip
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Shelf Life	52 Weeks
MSL	1

### Specifications

Capacitance	68 uF
Capacitance Tolerance	20%
Voltage DC	63 VDC, 72.45 VDC (Surge)
Temperature Range	-55/+135°C
Rated Temperature	135°C
Life	2000 Hrs
Dissipation Factor	8% 120Hz 20C
ESR	35 mOhms (100kHz 20C)
Ripple Current	1850 mAmps (100kHz 125C), 2100 mAmps (100kHz 135C), 5900 mAmps (100kHz 105C MAX, With Heat Sink), 3800 mAmps (100kHz 125C MAX, With Heat Sink)
Leakage Current	42.84 uA (2min 20°C)
High Temperature Solder	Yes