



Click [here](#) for the 3D model.

General Information	
Series	ALP22
Dielectric	Aluminum Electrolytic
Description	Solder Pin, Aluminum Electrolytic
RoHS	Yes
Lead	3 Pin Solder
AEC-Q200	No
Typical Component Weight	39 g
Notes	Dimensions D And L Include Slewing.

Specifications	
Capacitance	1,000 uF
Tolerance	20%
Voltage DC	100 VDC, 115 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	12000 Hrs
Leakage Current	600 uA (5min 20°C)

Dimensions	
D	25mm +/-1mm
L	45mm +/-2mm
S	12.5mm +/-0.1mm
LL	7.5mm +/-0.5mm
F	1.3mm

Packaging Specifications	
Slewing	Yes
Packaging	Tray