



Click [here](#) for the 3D model.

#### General Information

Series	ALF70
Dielectric	Aluminum Electrolytic
Style	Press-Fit
Description	Aluminum Electrolytic
RoHS	Yes
Lead	5 Pin Press-Fit
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	105 g
Notes	Dimensions D And L Include Slewing.
Shelf Life	156 Weeks

#### Specifications

Capacitance	750 uF
Tolerance	20%
Voltage DC	450 VDC, 495 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage At 85C)
ESR	195.4 mOhms (100Hz 20C), 111.9 mOhms (10kHz 20C)
Ripple Current	3.423 Amps (100Hz 85C), 7.333 Amps (10kHz 85C)
Leakage Current	2025 uA (5min 20°C)

#### Dimensions

D	40mm +1mm
L	50mm +/-2mm
S	25mm +/-0.1mm
LL	5.5mm +/-1mm
F	1.486mm +/-0.076mm

#### Packaging Specifications

Slewing	Yes
Packaging	Bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.