



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--|
| Series | ALS60 |
| Dielectric | Aluminum Electrolytic |
| Description | High Voltage, Screw Terminal, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | Oval Threaded Inserts M5 |
| Mounting | Through-Hole |
| AEC-Q200 | No |
| Typical Component Weight | 300 g |
| Notes | Dimensions D And L Include Slewing. MS (MxH) = M12x16. |

Specifications

| | |
|-------------------|--|
| Capacitance | 820 uF |
| Tolerance | 20% |
| Voltage DC | 550 VDC, 605 VDC (Surge) |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Life | 18000 Hrs |
| ESR | 366.9 mOhms (100Hz 20C), 325.4 mOhms (10kHz 20C) |
| Ripple Current | 5.66 Amps (100Hz 85C), 9.04 Amps (10kHz 85C) |
| Leakage Current | 2706 uA (5min 20°C) |

Dimensions

| | |
|----|-----------------|
| D | 51mm +/-1mm |
| L | 105mm +/-2mm |
| T | 5.5mm +/-0.5mm |
| S | 22.2mm +/-0.5mm |
| DT | 13mm +/-0.5mm |
| LT | 110.5mm +/-1mm |
| TD | 10mm MIN |
| V | 13.7mm NOM |
| Z | 10mm NOM |

Packaging Specifications

| | |
|-----------|-----------|
| Slewing | Yes |
| Packaging | Bulk, Box |