



Click [here](#) for the 3D model.

General Information

Series	ARR Indust X7R HT200C
Style	Radial
Description	Commercial, High Temperature
Features	Commercial
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	f2ec9c71-d741-45f9-8d01-f6de6baf235a
Termination	Gold
Lead	Wire Leads
Testing and Reliability	Standard
AEC-Q200	No

Dimensions

L	12.7mm MAX
W	12.7mm MAX
T	3.81mm MAX
S	10.16mm +/-0.38mm
LL	3.175mm MIN
F	0.635mm +/-0.051mm

Specifications

Capacitance	1.2 uF
Capacitance Tolerance	20%
Voltage DC	200 VDC
Temperature Range	-55/+200°C
Temperature Coefficient	X7R
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Insulation Resistance	833.3 MOhms

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.