



Click [here](#) for the 3D model.

#### General Information

Series	ALS36
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Screw Terminals 10-32 UNF 2B
Mounting	Through-Hole
AEC-Q200	No
Typical Component Weight	241 g
Notes	Add 0.015 in/ 0.4 mm to D and 0.045 in/ 1.1 mm to L for Sleaving. Dimension LT Available On Request. MS (MxH) = M12x16. Mounting Clamp (Sold Separately): V4/2737
Shelf Life	156 Weeks

#### Specifications

Capacitance	68,000 uF
Tolerance	-10/+30%
Voltage DC	25 VDC, 30 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	18000 Hrs (Rated Voltage And Ripple Current At 85C), 36000 Hrs (Rated Voltage at 85C)
ESR	14 mOhms (120Hz 25C), 12 mOhms (20kHz 25C)
Ripple Current	16.3 Amps (120Hz 85C), 17.6 Amps (20kHz 85C)
Leakage Current	6000 uA (5min 20°C)

#### Dimensions

D	50.8mm +/-0.787mm
L	79.375mm +/-1.575mm
T	7.137mm +/-0.787mm
S	22.225mm +/-0.483mm
DT	8.001mm +/-0.483mm
TD	10.008mm MIN
V	13.691mm NOM

#### Packaging Specifications

Packaging	Bulk, Box
-----------	-----------